



Main

Range	Ultimate
Product or component type	Switched socket with USB charger
Device presentation	Complete product
Colour tint	White front plate
Surface finish	Metallic
Connections - terminals	Screw terminals
Switch function	1-pole

Complementary

Device mounting	Flush Surface
Integrated connection type	USB port 2 5 V DC 2.1 A Socket-outlet 2 250 V AC 13 A 50/60 Hz
Actuator	Rocker
Number of gangs	2 gangs
Pilot light	Without LED
Fixing mode	Screw M3.5 2 26 mm Screw M3.5 2 32 mm
Clamping connection capacity	2 x 6 mm ² solid 3 x 4 mm ² solid 5 x 2.5 mm ² solid 3 x 4 mm ² stranded 5 x 2.5 mm ² stranded
Material	Steel
Product compatibility	Mobile/tablet Apple Mobile/tablet Samsung Mobile/tablet LG Mobile/tablet Blackberry Mobile/tablet HTC Mobile/tablet Sony Mobile/tablet Huawei Technologies
Directives	2004/108/EC - electromagnetic compatibility 2006/95/EC - low voltage directive
Quality labels	CE
Quantity per set	Set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Type of packing	Bag
Type of installation	Indoor
Depth	5.5 mm
Width	147.7 mm
Height	87.7 mm

Environment

IP degree of protection	IP20
Standards	BS 1363-2