

## Product data sheet

### Characteristics

# GGBL6032CPCS

Lisse - Universal Dimmer - 3 gang 2 way - 250W/  
VA Polished Chrome



### Main

Range	Lisse
Aesthetic name	Screwless deco
Product or component type	Dimmer
Device presentation	Complete product
Load type	230 V AC halogen lamp Incandescent lamp: 250 W
Colour tint	Polished chrome
Quantity per set	Set of 1

### Complementary

Device mounting	Wall mounted
Dimmer application	Inductive load Resistive load
[Ue] rated operational voltage	230 V AC 50 Hz
Number of gangs	3 gangs
Connections - terminals	Screw terminals
Fixing mode	Concealed screws
Material	Stainless steel
Type of packing	Bag
Height	87 mm
Width	148 mm
Depth	44 mm
Net weight	0.296 kg

### Environment

Standards	BS EN 60669-2-1
IP degree of protection	IP20

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>

Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins