

Product data sheet

Specifications



Switch with flex outlet, Ultimate Low profile, 2-pole, screw terminals, IP20, chrome

GU2513WBC

Main

Range Of Product	Ultimate
Range	Ultimate
Aesthetic Name	Low profile
Product Or Component Type	Switch with flex outlet
Switch Function	2-pole
Rated Current	20 AX at 230 V AC

Complementary

Connections - Terminals	Screw terminals
Quantity Per Set	Set of 1
Number Of Gangs	1 gang
Height	88 mm
Width	88 mm

Environment

Standards	BS EN 60669-1
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	9.500 cm
Package 1 Length	9.600 cm
Package 1 Weight	180.700 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	100
Package 2 Height	21.500 cm
Package 2 Width	42.500 cm
Package 2 Length	50.000 cm
Package 2 Weight	18.801 kg
Unit Type Of Package 3	PAM

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 3	1600
Package 3 Height	102.500 cm
Package 3 Width	120.000 cm
Package 3 Length	100.000 cm
Package 3 Weight	320.819 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration