



Main

Aesthetic name	Flat plate
Product or component type	Switched socket
Rated current	13 A 230 V AC 50 Hz
Fixing mode	By screws M3.5 30 mm
Colour tint	Chrome

Complementary

Device presentation	Complete product
Outlet poles configuration	2P
Outlet standard description	3 pins
Outlet standard	British
Actuator	Rocker
Number of gangs	2 gangs
Earth circuit	Standard earth
Pilot light	Neon indicator
Device mounting	Wall mounted
Connections - terminals	Screw terminal
Material	Steel
Quantity per set	Set of 1
Height	88 mm
Width	148 mm
Depth	30 mm

Environment

IP degree of protection	IP20
Standards	BS 1363

Contractual warranty

Warranty period	18 months
-----------------	-----------