

# Product data sheet

Specifications



## Ultimate Flat plate - switched socket - 2P - 2 gangs - white metal

GU3234WPW

⚠ Discontinued on: Jan 1, 2006

⚠ Discontinued

### Main

|                           |                        |
|---------------------------|------------------------|
| Aesthetic Name            | Flat plate             |
| Product Or Component Type | Switched socket        |
| Rated Current             | 13 A at 230 V AC 50 Hz |
| Fixing Mode               | By screws M3.5 x 30 mm |
| Colour Tint               | White metal            |

### Complementary

|                             |                  |
|-----------------------------|------------------|
| Device Presentation         | Complete product |
| Outlet Poles Configuration  | 2P               |
| Outlet Standard Description | 3 pins           |
| Outlet Standard Deviation   | British          |
| Actuator                    | Rocker           |
| Number Of Gangs             | 2 gangs          |
| Earth Circuit               | Standard earth   |
| Pilot Light                 | Neon indicator   |
| Device Mounting             | Wall mounted     |
| Connections - Terminals     | Screw terminal   |
| Material                    | Steel            |
| Quantity Per Set            | Set of 1         |
| Height                      | 88 mm            |
| Width                       | 148 mm           |
| Depth                       | 30 mm            |

### Environment

|                         |         |
|-------------------------|---------|
| Ip Degree Of Protection | IP20    |
| Standards               | BS 1363 |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications