



Main

Aesthetic name	Flat plate
Product or component type	Unswitched socket
Rated current	13 A 230 V AC 50 Hz
Fixing mode	By screws M3.5 30 mm
Colour tint	Brass

Complementary

Device presentation	Complete product
Outlet poles configuration	1P
Outlet standard description	3 pins
Outlet standard	British
Number of gangs	2 gangs
Earth circuit	Standard earth
Pilot light	Without neon indicator
Device mounting	Wall mounted
Connections - terminals	Screw terminal
Material	Steel
Quantity per set	Set of 1
Height	88 mm
Width	148 mm
Depth	26 mm

Environment

IP degree of protection	IP20
Standards	BS 1363

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1639 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------
