


Product data sheet

Specifications



Ultimate Flat plate - unswitched socket - 2 gangs - brass

GU3260WPB

⚠ Discontinued on: Dec 17, 2020

⚠ Discontinued

Main

Aesthetic Name	Flat plate
Product Or Component Type	Socket-outlet
Rated Current	13 A at 230 V AC 50 Hz
Fixing Mode	By screws M3.5 x 30 mm
Colour Tint	Brass

Complementary

Device Presentation	Complete product
Outlet Poles Configuration	1P
Outlet Standard Description	3 pins
Outlet Standard	British
Number Of Gangs	2 gangs
Earth Circuit	Standard earth
Pilot Light	Without neon indicator
Device Mounting	Wall mounted
Connections - Terminals	Screw terminal
Material	Steel
Quantity Per Set	Set of 1
Height	88 mm
Width	148 mm
Depth	26 mm

Environment

Ip Degree Of Protection	IP20
Standards	BS 1363

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.1 cm
Package 1 Width	4.1 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	16.3 cm
Package 1 Weight	239 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation
