



Main

Aesthetic name	Flat plate
Product or component type	Unswitched socket
Rated current	5 A at 230 V AC 50 Hz
Fixing mode	By screws M3.5 x 30 mm
Colour tint	Brass

Complementary

Device presentation	Complete product
Outlet poles configuration	1P
Outlet standard description	Round pin
Number of gangs	1 gang
Earth circuit	Standard earth
Pilot light	Without neon indicator
Device mounting	Wall mounted
Connections - terminals	Screw terminal
Material	Steel
Quantity per set	Set of 1
Height	88 mm
Width	88 mm
Depth	26 mm
Socket number	2

Environment

IP degree of protection	IP20
Standards	BS 546

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------
