

Product data sheet

Specifications



Ultimate Flat plate - switched socket - 1 gang - pearl nickel

GU3290WPN

⚠ Discontinued on: Oct 9, 2019

⚠ Discontinued

Main

| | |
|---------------------------|------------------------|
| Aesthetic Name | Flat plate |
| Product Or Component Type | Switched socket |
| Rated Current | 15 A at 230 V AC 50 Hz |
| Fixing Mode | By screws M3.5 x 30 mm |
| Colour Tint | Pearl nickel |

Complementary

| | |
|-----------------------------|------------------------|
| Device Presentation | Complete product |
| Outlet Poles Configuration | 1P |
| Outlet Standard Description | Round pin |
| Actuator | Rocker |
| Number Of Gangs | 1 gang |
| Earth Circuit | Standard earth |
| Pilot Light | Without neon indicator |
| Device Mounting | Wall mounted |
| Connections - Terminals | Screw terminal |
| Material | Steel |
| Quantity Per Set | Set of 1 |
| Height | 88 mm |
| Width | 88 mm |
| Depth | 30 mm |
| Socket Number | 2 |

Environment

| | |
|-------------------------|--------|
| Ip Degree Of Protection | IP20 |
| Standards | BS 546 |

Packing Units

| | |
|------------------------------|--------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.1 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|---------|
| Package 1 Width | 9.1 cm |
| Package 1 Length | 10.2 cm |
| Package 1 Weight | 148 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|