



### Main

Aesthetic name	Screwless flat plate
Product or component type	Unswitched socket
Rated current	13 A 230 V AC 50 Hz
Fixing mode	By screws M3.5 30 mm
Colour tint	Brass

### Complementary

Device presentation	Complete product
Outlet poles configuration	1P
Outlet standard description	3 pins
Outlet standard	British
Number of gangs	1 gang
Earth circuit	Standard earth
Pilot light	Without neon indicator
Device mounting	Wall mounted
Connections - terminals	Screw terminal
Material	Steel
Quantity per set	Set of 1
Height	88 mm
Width	88 mm
Depth	26 mm
Socket number	2

### Environment

IP degree of protection	IP20
Standards	BS 1363

### Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant <a href="#">Will not be compliant</a>
REACH	Reference not containing SVHC above the threshold

Reference not containing SVHC above the threshold

---

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---