

Product data sheet

Specifications



Ultimate Slimline - 2-way pushbutton dimmer - 4 gangs - white

GU6042LV

⚠ Discontinued on: Jan 1, 2006

⚠ Discontinued

Main

Range Of Product	Ultimate
Aesthetic Name	Slimline
Product Or Component Type	Push-button dimmer
Load Type	Low voltage lamps with electronic transformer: 250 VA Incandescent lamp
Colour Tint	White moulded matt
Quantity Per Set	Set of 1

Complementary

Switch Function	2-way
Device Mounting	Wall mounted
Dimmer Application	Inductive load Resistive load
[Ue] Rated Operational Voltage	230 V AC 50 Hz
Number Of Gangs	4 gangs
Connections - Terminals	Screw terminals
Material	Urea (carbamide)
Height	86 mm
Width	146 mm
Depth	20 mm

Environment

Standards	BS EN 60669-2-1
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.8 cm
Package 1 Width	9.5 cm
Package 1 Length	15.8 cm
Package 1 Weight	259 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------