

# Product data sheet

Specifications



## Ultimate Screwless flat plate - shaver socket - stainless steel/white

GU7490WSS

### Main

|                           |                               |
|---------------------------|-------------------------------|
| Range Of Product          | Ultimate                      |
| Aesthetic Name            | Screwless flat plate          |
| Product Or Component Type | Shaver socket                 |
| Input Voltage             | 230 V AC 50 Hz                |
| Colour Tint               | Stainless steel matt<br>White |

### Complementary

|                         |                        |
|-------------------------|------------------------|
| Material                | Steel                  |
| Fixing Mode             | By screws M3.5 x 30 mm |
| Device Mounting         | Flush                  |
| Connections - Terminals | Screw terminals        |
| Quantity Per Set        | Set of 1               |
| Height                  | 148 mm                 |
| Width                   | 88 mm                  |
| Depth                   | 47 mm                  |

### Environment

|                         |                 |
|-------------------------|-----------------|
| Standards               | BS EN 61558-2-5 |
| Ip Degree Of Protection | IP20            |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 5.5 cm  |
| Package 1 Width              | 10.2 cm |
| Package 1 Length             | 16 cm   |
| Package 1 Weight             | 856 g   |
| Unit Type Of Package 2       | CAR     |
| Number Of Units In Package 2 | 20      |
| Package 2 Height             | 18 cm   |
| Package 2 Width              | 30 cm   |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |          |
|------------------------------|----------|
| Package 2 Length             | 42.5 cm  |
| Package 2 Weight             | 17.5 kg  |
| Unit Type Of Package 3       | PAM      |
| Number Of Units In Package 3 | 800      |
| Package 3 Height             | 106.5 cm |
| Package 3 Width              | 100 cm   |
| Package 3 Length             | 120 cm   |
| Package 3 Weight             | 720 kg   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

|  |  |
|--|--|
|  Rohs Exemption Information | Yes                                    |
| <hr/>  |  |
| Reach Regulation   | <a href="#">REACH Declaration</a>      |
| <hr/>  |  |
| Eu Rohs Directive  | Compliant with Exemptions              |
| <hr/>  |  |
| China Rohs Regulation  | <a href="#">China RoHS declaration</a> |
| <hr/>  |  |