

Product data sheet

Specifications



Ultimate - low profile plate Grid system - 4 gangs - white metal

GUG04GPW

Main

Range	Ultimate
Device Application	Mounting
Aesthetic Name	Grid system
Product Or Component Type	Front plate
Range Compatibility	Ultimate front plate
Mounting Mode	Flush-mounted
Colour Tint	Painted white matt

Complementary

Installation Direction	Horizontal/vertical
Number Of Gangs	4 gangs
Fixing Mode	By screws
Material	Stainless steel
Quantity Per Set	Set of 1
Width	88 mm
Height	148 mm

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.409 cm
Package 1 Width	6.409 cm
Package 1 Length	6.409 cm
Package 1 Weight	185.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	9.700 cm
Package 2 Width	15.600 cm
Package 2 Length	8.700 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	999.000 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	21.000 cm
Package 3 Width	34.000 cm
Package 3 Length	45.000 cm
Package 3 Weight	20.334 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability


Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Rohs Exemption Information	Yes
<hr/>	
Reach Regulation	REACH Declaration
<hr/>	
Eu Rohs Directive	Compliant with Exemptions
<hr/>	
China Rohs Regulation	China RoHS declaration
<hr/>	