

Product data sheet

Specifications



Blank plate, Ultimate, 1 gang, stainless steel & white interior

GUGBWSS

Main

Range	Ultimate
Accessory / Separate Part Category	Wiring accessory
Aesthetic Name	Grid system
Product Or Component Type	Blank plate
Colour Tint	White Stainless steel
Quantity Per Set	Set of 1

Complementary

Range Compatibility	Ultimate blank plate
Device Mounting	Wall mounted
Fixing Mode	Snap-fitted
Number Of Gangs	1 gang
Number Of Modules	1 module
Surface Finish	Matt
Material	Nylon Steel PC (polycarbonate)
Height	59 mm
Width	25 mm
Depth	22 mm
Net Weight	0.008 kg

Environment

Standards	BS 1363 BS 5733
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.400 cm
Package 1 Width	2.700 cm
Package 1 Length	6.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	8.500 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	6.600 cm
Package 2 Width	6.500 cm
Package 2 Length	8.500 cm
Package 2 Weight	69.000 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	600
Package 3 Height	15.500 cm
Package 3 Width	45.500 cm
Package 3 Length	67.000 cm
Package 3 Weight	8.014 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability


Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Rohs Exemption Information	Yes
<hr/>	
Reach Regulation	REACH Declaration
<hr/>	
Eu Rohs Directive	Compliant with Exemptions
<hr/>	
China Rohs Regulation	China RoHS declaration
<hr/>	