

Product data sheet

Specifications



Enclosure for TeSys GV2ME, TeSys GV2 IP55, fitted with Emergency stop

GV2MCK04

Main

Range	TeSys
Product Or Component Type	Enclosure
Device Short Name	GV2MC
Accessory / Separate Part Category	Mounting accessory
Product Compatibility	GV2ME
Enclosure Type	Surface mounting
Provided Equipment	Mushroom head emergency stop push-button

Complementary

Auxiliary Mounting Location	Right Left
Height	147 mm
Width	93 mm
Depth	145.5 mm
Net Weight	0.3 kg

Environment

Ip Degree Of Protection	IP55
Environmental Characteristic	Standard environment
Product Certifications	UKCA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.000 cm
Package 1 Width	15.500 cm
Package 1 Length	16.500 cm
Package 1 Weight	396.000 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	19
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	60.000 cm
Package 2 Weight	8.168 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations