



GV2ME07K1FE7 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

### Main

Range	TeSys
Device short name	GV2ME
Product or component type	Motor starter
Motor starter type	Non reversing
Poles description	3P
Utilisation category	AC-3
Motor power kW	0.75 kW at 440 V AC 50/60 Hz 0.75 kW at 400/415 V AC 50/60 Hz 1.1 kW at 440 V AC 50/60 Hz 1.1 kW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	115 V AC 50/60 Hz
Magnetic tripping current	33.5 A

### Complementary

Device composition	1 3-pole contactor 1 combination block GV2AF01 1 motor circuit breaker type GV2ME
Coordination type	Type 1
Thermal protection adjustment range	1.6...2.5 A
Breaking capacity	I <sub>q</sub> = 50 kA at 400/415 V AC 50/60 Hz conforming to IEC 60947-4-1 I <sub>q</sub> = 50 kA at 440 V AC 50/60 Hz conforming to IEC 60947-4-1 I <sub>q</sub> = 50 kA at 500 V AC 50/60 Hz conforming to IEC 60947-4-1
Product weight	0.46 kg
Height	152 mm
Width	45 mm
Depth	87 mm

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0840 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
------------------------	---------------------------------------------------------------------------------------------------------------------------------------

### Contractual warranty

Warranty period	18 months
-----------------	-----------