



### Main

|                              |  |
|------------------------------|--|
| Range                        | TeSys  |
| Device short name            | GV2ME  |
| Product or component type    | Motor starter  |
| Motor starter type           | Non reversing  |
| Poles description            | 3P   |
| Utilisation category         | AC-3   |
| Motor power kW               | 3 kW at 500 V AC 50/60 Hz<br>2.2 kW at 400/415 V AC 50/60 Hz<br>2.2 kW at 440 V AC 50/60 Hz<br>3 kW at 440 V AC 50/60 Hz |
| [Uc] control circuit voltage | 400 V AC 50/60 Hz  |
| Magnetic tripping current    | 78 A   |

### Complementary

|                                     |   |
|-------------------------------------|---|
| Device composition                  | 1 3-pole contactor<br>1 combination block GV2AF01<br>1 motor circuit breaker type GV2ME   |
| Coordination type                   | Type 1  |
| Thermal protection adjustment range | 4...6.3 A   |
| Breaking capacity                   | 50 kA I <sub>q</sub> at 400/415 V AC 50/60 Hz conforming to IEC 60947-4-1<br>50 kA I <sub>q</sub> at 440 V AC 50/60 Hz conforming to IEC 60947-4-1<br>50 kA I <sub>q</sub> at 500 V AC 50/60 Hz conforming to IEC 60947-4-1 |
| Net weight                          | 0.46 kg   |
| Height                              | 152 mm  |
| Width                               | 45 mm   |
| Depth                               | 87 mm   |

### Offer Sustainability

|                          |                       |
|--------------------------|-----------------------|
| Sustainable offer status | Green Premium product |
|--------------------------|-----------------------|

|                            |   |
|----------------------------|---|
| REACH Regulation           | <a href="#">REACH Declaration</a>   |
| EU RoHS Directive          | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information       |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile        | No need of specific recycling operations  |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|