

Product data sheet

Specifications



non reversing enclosed DOL starter TeSys - GVN-GC - 25...63 A

GVNGC02R

! Discontinued

Main

Range Of Product	TeSys
Device Short Name	GVNGC
Motor Starter Type	Non reversing
Product Or Component Type	Enclosed DOL starter
Poles Description	3P
Motor Starter Composition	Without circuit breaker
Thermal Protection Adjustment Range	25...63 A
Control Type	Rotary handle red
Enclosure Material	Polycarbonate

Complementary

[Ue] Rated Operational Voltage	500 V
Cable Entry	2 x 40 mm ISO at top 2 x 25 mm ISO at top 2 x 20 mm ISO at top 2 x 40 mm ISO at bottom 2 x 32 mm ISO at bottom 2 x 25 mm ISO at bottom 2 x 32 mm ISO at top 2 x 20 mm ISO at bottom
Width	186.3 mm
Height	348 mm
Depth	237 mm
Net Weight	0.55 kg

Environment

Standards	IEC 60947-4 VDE 0660-102 IEC 60439-1 EN 60947
Ip Degree Of Protection	IP407 conforming to IEC 60529

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications