



Main

Range of product	EcoStruxure operator terminal Expert
Product or component type	License
Language	Multi-language
Format	Paper
Previous software version	V3.0

Complementary

Range compatibility	Magelis STO7 Magelis GTU Magelis GTO Magelis iPC Magelis ST6
Software designation	EcoStruxure Operator Terminal Expert
Type of license	Group (3 seats)
Software version	V3.1
System requirements	> 1 GB HDD storage device Windows 7 Professional 32/64 bit, > 4 GB primary memory > 1 GB HDD storage device Windows 8.1, > 4 GB primary memory > 1 GB HDD storage device Windows 10, > 4 GB primary memory > 1 GB HDD storage device Windows Embedded standard 7 32/64 bit, > 4 GB primary memory
Communication port protocol	Q series CPU direct IQ-R/F series Ethernet Uni-Telway CS/CJ/NJ series Ethernet/IP Modbus SIO slave Ethernet/IP Modbus TCP slave Q series QnU CPU Ethernet Modbus SIO ASCII master CS/CJ series HOST link FX series Ethernet Profibus DP slave Modbus SIO master CS/CJ series Ethernet FX series CPU direct Q/QnA series serial FX series computer link Modbus TCP master DF1 CANopen slave PacDrive

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ROC Plus SIO
Zelio Logic
Simatic S7 MPI direct
Q/QnA Series Ethernet
Simatic S7 Ethernet
ROC Plus Ethernet
DH485
SoMachine network
A series Ethernet
TIA portal Ethernet
Controller NX1 via Ethernet/IP
Controller NX1P via Ethernet/IP
Controller NX7 via Ethernet/IP

Provided equipment	User's documentation in electronic format EcoStruxure operator terminal Expert
Software function	26 type of fonts 65535 alarms 65535 variables

Environment

Image import standard	PNG
-----------------------	-----
