



### Main

Range of product	EcoStruxure operator terminal Expert
Product or component type	License
Language	Multi-language
Format	Paper
Previous software version	V3.0

### Complementary

Range compatibility	Magelis iPC
Software designation	EcoStruxure Operator Terminal Expert
Type of license	Single (1 seat)
Software version	V3.1
System requirements	> 1 GB HDD storage device Windows 7 Professional 32/64 bit, > 2 GB primary memory > 1 GB HDD storage device Windows 8.1, > 2 GB primary memory > 1 GB HDD storage device Windows 10, > 2 GB primary memory > 1 GB HDD storage device Windows Embedded standard 7 32/64 bit, > 2 GB primary memory
Communication port protocol	CS/CJ/NJ series Ethernet/IP SoMachine network CANopen slave CS/CJ series Ethernet Zelio Logic DH485 Modbus SIO master Q/QnA Series Ethernet Modbus SIO ASCII master Q/QnA series serial FX series CPU direct Simatic S7 Ethernet Profibus DP slave Simatic S7 MPI direct DF1 FX series Ethernet ROC Plus SIO Uni-Telway FX series computer link PacDrive Q series QnU CPU Ethernet Q series CPU direct ROC Plus Ethernet Modbus SIO slave Ethernet/IP

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Modbus TCP master  
IQ-R/F series Ethernet  
Modbus TCP slave  
CS/CJ series HOST link  
A series Ethernet  
TIA portal Ethernet  
Controller NX1 via Ethernet/IP  
Controller NX1P via Ethernet/IP  
Controller NX7 via Ethernet/IP

---

Provided equipment	EcoStruxure operator terminal Expert User's documentation in electronic format
Software function	65535 variables 65535 alarms 26 type of fonts

---

## Environment

---

Image import standard	PNG
-----------------------	-----

---