



Main

Range of product	PacDrive 3
Product or component type	Detached servo drive
Device short name	ILD

Complementary

Product compatibility	Servo motor MH3 Motor asynchronous motor Servo motor SH3 <= 6 A Servo motor SH3 <= 4.4 A
[Us] rated supply voltage	250...700 V
[In] rated current	6 A with active cold plate cooling 4.4 A with passive cold plate cooling
Safety function	STO (safe torque off)
Type of cooling	Fanless Water cooled Passive cold plate
Number of mounting holes	4
Product weight	5.3 kg

Environment

IP degree of protection	IP65
Standards	EN/IEC 61800-5-1 EN/IEC 61800-5-2 EN/IEC 62061 UL 618000-5-1 EN/IEC 61800-3 EN/ISO 13849-1 CSA C22.2 No 274
Directives	2006/42/EC - machinery 2014/30/EU - electromagnetic compatibility 2014/35/EU - low voltage directive
Product certifications	cURus CE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications