



Main

Range of product	Mureva
Product name	Mureva BOX
Product or component type	Junction box
Device application	Cable installation
Colour tint	White (RAL 9003)
Quantity per set	Set of 5

Complementary

Device mounting	Surface
Fixing mode	By screw : body housing
Base dimension	65 x 55 x 105 mm
Cable entry	Grommets
Cable entry number	8 x 20 mm
Material	ABS (acrylonitrile butadiene-styrene) : body PP (polypropylene) : cover
Terminals	Without terminal
Height	65 mm
Width	105 mm
Depth	55 mm

Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP55
IK degree of protection	IK07
Glow wire temp	650 °C
Standards	CE EN 60670

Environmental characteristic	Halogen free
------------------------------	--------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
