

Product data sheet

Specifications



Thorsman BS Socket Tester

IMT23103

⚠ Discontinued on: Dec 19, 2023

⚠ Discontinued

Main

Product Or Component Type	Socket-outlet tester
Outlet Standard	British

Complementary

Local Signalling	Ground error by LCD display
Function Available	RCD test function
Rated Voltage	220 V 50...60 Hz +/- 10 %
Measurement Category	Category III 300 V
Residual Test Current	30 mA +/- 15 %
Rcd Test Time	60...300 ms
Contact Voltage Threshold	< 35 V AC
Height	77 mm
Width	67 mm
Depth	66 mm
Net Weight	70 g

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	13.3 cm
Package 1 Length	19.4 cm
Package 1 Weight	125.7 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	20
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2.941 kg
Unit Type Of Package 3	P12

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 3	480
Package 3 Height	105 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	82.584 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration