



Main

Range	Thorsman
Product or component type	LED detector
Supply	Battery 9 V 6F22

Complementary

Display type	LED indicator
Type of setting	Manual
Device composition	Detector
Local signalling	Object detection by spotlight Top edge of object detection by LED indicator
Detection depth	Metal mode : iron pipe detection of 25 mm <= 30 mm AC mode : <= 50 mm for 90...250 V @ 50...60 Hz Stud mode : wood stud detection of 30 x 30 mm <= 18 mm
Language	Danish English Finnish Norwegian Swedish
Height	150 mm
Width	66 mm
Depth	32 mm
Product weight	165 g with battery