

# Product data sheet

Specifications



## Thorsman IR Thermometer 520°C

IMT23107

### Main

Range	Thorsman
Product Or Component Type	Thermometer
Supply	battery 9 V
Technology Type	Laser

### Complementary

Display Type	Handheld infrared thermometer: backlit LCD
Measurement Temperature	Handheld infrared thermometer: -20...520 °C
Language	Swedish English Danish Finnish Norwegian
Height	180 mm
Width	85 mm
Depth	50 mm
Product Weight	150 g without battery

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	17.000 cm
Package 1 Length	29.000 cm
Package 1 Weight	245.000 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	20
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	5.420 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	80

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	33.680 kg

# Sustainability




**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Compliant
		<a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a>