

Product data sheet

Specifications

Thorsman Voltage Detector Pen

IMT23109



Main

Range	Thorsman
Product Or Component Type	Voltage tester
Supply	2 battery 1.5 V AAA

Complementary

Local Signalling	Presence of voltage: LED Presence of voltage: alarm sound indicator
Measurement Voltage	5...1000 V AC
Network Frequency	50...400 Hz
Measurement Category	Category IV 1000 V
Language	Norwegian Finnish English Danish Swedish
Height	152 mm
Width	32 mm
Depth	28 mm
Net Weight	50 g

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22.5 cm
Package 1 Width	4.0 cm
Package 1 Length	11.7 cm
Package 1 Weight	97.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	25
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.866 kg
Unit Type Of Package 3	P12

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 3	600
Package 3 Height	105.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	80.784 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	