

# Product data sheet

Specifications



## Thorsman Analogue Multimeter Cat III

IMT23113

⚠ Discontinued on: Dec 19, 2023

⚠ Discontinued

### Main

Range	Thorsman
Product Or Component Type	Analog multimeter
Supply	battery 1.5 V

### Complementary

Type Of Setting	Manual
Function Available	Handsfree operations
Protection Type	Fuse
Type Of Measurement	Resistance: x10 Ohm/x1 kOhm Voltage DC: 12/60/120/300 V Voltage AC: 12/60/300 V Current DC: 0.6/12/600 mA
Measurement Category	Category III 300 V
Relative Humidity	0...85 %
Language	Norwegian Swedish Danish Finnish English
Height	140 mm
Width	75 mm
Depth	50 mm
Product Weight	275 g without battery

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	15 cm
Package 1 Length	26 cm
Package 1 Weight	351.5 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	34 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	16.5 cm
Package 2 Length	35 cm
Package 2 Weight	3.758 kg

## Sustainability




**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Compliant
		<a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a>