



Main

Range	Thorsman
Product or component type	Test meter
Supply	2 battery 3 V

Complementary

Display digits	3.5
Type of setting	Automatic reset
Signaling function	Low battery by visual
Function available	Data hold function Audible continuity High precision measuring Tactile barrier for safety
Type of measurement	Voltage DC : 200mV/2/20/200/600 V Resistance : 200 Ohm/2/20/200 kOhm/20 MOhm Voltage AC : 2/20/200/600 V Current AC : 2/20/200/600 A Continuity : < 30 Ohm Diode check : 1.5 V
Measurement category	Category III 600 V
Language	Danish English Finnish Norwegian Swedish
Height	190 mm
Width	76 mm
Depth	36 mm
Product weight	160 g with battery

Environment

Standards	IEC 61010
-----------	-----------