

Product data sheet

Specifications



Thorsman Digital Multimeter Cat III 300V

IMT23202

Main

Range	Thorsman
Product Or Component Type	Digital multimeter
Supply	battery 9 V

Complementary

Display Type	Backlit monochrome STN LCD
Type Of Setting	Manual
Signaling Function	Low battery by visual
Function Available	Stand alone equipment control Non-contact AC voltage detection Data hold function Live AC wire detection
Protection Type	Fuse
Type Of Measurement	Resistance: 200 Ohm/2/20/200 kOhm/20 MOhm Battery voltage: 1.5/9 V/12 V Continuity: < 100 Ohm Voltage DC: 0.2/2/20/200/300 V Voltage AC: 0.2/2/20/200/300 V Current DC: 20 mA/200 mA/10 A Temperature: 0...1000 °C
Measurement Category	Category III 300 V
Language	German Spanish French Polish Portuguese
Height	165 mm
Width	85 mm
Depth	39 mm
Product Weight	290 g with battery

Environment

Standards	IEC 61010
-----------	-----------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	17.500 cm
Package 1 Length	26.500 cm
Package 1 Weight	447.500 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.809 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	192
Package 3 Height	90.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	104.944 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging

Resource performance

✔ Sustainable Packaging

Well-being performance

✔ Reach Free Of Svhc

✔ Toxic Heavy Metal Free

✔ Mercury Free

✔ Rohs Exemption Information Yes

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)