

# Product data sheet

Specifications



## Thorsman Multifunction Cable Tracer

IMT23206

### Main

Range	Thorsman
Product Or Component Type	Multi-function wire tracer
Supply	Receiver 4 battery 1.5 V LR41/SR41 Transmitter 2 battery 1.5 V AAA

### Complementary

Device Composition	Transmitter - to generate a distinct tone in wire Receiver - to pick up the tone
Local Signaling	LED operating
Language	Spanish German Polish Hungarian Portuguese French
Height	183 mm
Width	80 mm
Depth	46 mm
Product Weight	220 g with battery

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	17.4 cm
Package 1 Length	29.5 cm
Package 1 Weight	304 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.352 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Sustainable Packaging

## Resource performance

✔ Sustainable Packaging

## Well-being performance

✔ Reach Free Of Svhc

✔ Toxic Heavy Metal Free

✔ Mercury Free

✔ Rohs Exemption Information      Yes

Reach Regulation      [REACH Declaration](#)

Eu Rohs Directive      Compliant  
[EU RoHS Declaration](#)

China Rohs Regulation      [China RoHS declaration](#)