

Product data sheet

Specifications

Thorsman Moisture Meter



IMT23208

Main

Range	Thorsman
Product Or Component Type	Moisture meter
Supply	4 battery LR44

Complementary

Display Type	LCD display LED indicator
Signaling Function	Low battery
Function Available	Temperature unit exchange (°C/°F) Automatic power off
Measurement Range	Wood: 6...60 % Building material: 0.2...2.9 %
Language	Hungarian Spanish German Polish French
Height	85 mm
Width	45 mm
Depth	16 mm
Product Weight	41 g with battery

Environment

Ambient Air Temperature For Operation	-0...37 °C 0...40 °C
---------------------------------------	-------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	11.1 cm
Package 1 Length	17.3 cm
Package 1 Weight	75.1 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	60
Package 2 Height	30 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.641 kg
Unit Type Of Package 3	PAM
Number Of Units In Package 3	1800
Package 3 Height	106.5 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	173.684 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Sustainable Packaging

Resource performance

✔ Sustainable Packaging

Well-being performance

✔ Reach Free Of Svhc

✔ Toxic Heavy Metal Free

✔ Mercury Free

✔ Rohs Exemption Information Yes

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)