

Product data sheet

Specifications



Thorsman Compact Digital Multimeter Cat III

IMT23212

Main

Range	Thorsman
Product Or Component Type	Digital multimeter
Supply	battery 12 V

Complementary

Type Of Setting	Manual
Signaling Function	Low battery by visual
Function Available	Handsfree operations
Protection Type	Fuse
Type Of Measurement	Current DC: 200 mA Voltage AC/DC: 2/20/200/300 V Resistance: 2/20/200 kOhm/2 MOhm
Measurement Category	Category III 300 V
Language	German Polish French Spanish Portuguese
Height	120 mm
Width	75 mm
Depth	18 mm
Product Weight	110 g with battery

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	11.2 cm
Package 1 Length	19.4 cm
Package 1 Weight	162.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	42
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	40.0 cm
Package 2 Weight	7.484 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Sustainable Packaging

Resource performance

✔ Sustainable Packaging

Well-being performance

✔ Reach Free Of Svhc

✔ Toxic Heavy Metal Free

✔ Mercury Free

✔ Rohs Exemption Information Yes

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)