



### Main

|                           |               |
|---------------------------|---------------|
| Range                     | Thorsman      |
| Product or component type | Test meter    |
| Supply                    | 2 battery 3 V |

### Complementary

|                      |   |
|----------------------|---|
| Display digits       | 3.5   |
| Type of setting      | Automatic reset   |
| Signaling function   | Low battery by visual   |
| Function available   | Data hold function<br>Audible continuity<br>High precision measuring<br>Tactile barrier for safety  |
| Type of measurement  | Voltage DC : 200mV/2/20/200/600 V<br>Resistance : 200 Ohm/2/20/200 kOhm/20 MOhm<br>Voltage AC : 2/20/200/600 V<br>Current AC : 2/20/200/600 A<br>Continuity : < 30 Ohm<br>Diode check : 1.5 V |
| Measurement category | Category III 600 V  |
| Language             | French<br>German<br>Hungarian<br>Polish<br>Portuguese<br>Spanish  |
| Height               | 190 mm  |
| Width                | 76 mm   |
| Depth                | 36 mm   |
| Product weight       | 160 g with battery  |

### Environment

|           |           |
|-----------|-----------|
| Standards | IEC 61010 |
|-----------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications