

Product data sheet

Specifications



Thorsman - Goliath 250 work lamp - 55 W - AUS/NZ plug

IMT33001

⚠ Discontinued on: Oct 22, 2018

⚠ End-of-service on: Nov 21, 2018

⚠ Discontinued

Main

Range	Thorsman
Product Name	Goliath 250
Product Or Component Type	Work lamp
Light Source	Compact fluorescent tube 55 W

Complementary

Type Of Installation	Outdoor Indoor
[Ue] Rated Operational Voltage	230...240 V
Plug Pole Configuration	2P + E
Plug Standard	New Zealand Australian
Light Source Type	Flicker-proof Glare-proof
Luminous Flux	4000 lm
Bulb Lifespan	8000 h
Colour Rendering Index	R _a =82
Illuminance	1 m: 1890 lux 3 m: 210 lux
Cable Insulation Material	Neoprene
Housing Material	PC + rubber
Electrical Connection	Feed power cord H07RN-F2x1.0 5 m
Electrical Insulation Class	Class II
Marking	F ENEC 14
Height	316 mm
Width	316 mm
Depth	91 mm
Net Weight	2.9 kg

Environment

Environmental Characteristic	Dustproof Waterproof
------------------------------	-------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP65
Quality Labels	ENEC
Ambient Air Temperature For Operation	-15...50 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	31 cm
Package 1 Width	13 cm
Package 1 Length	30.8 cm
Package 1 Weight	3100 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Certifications & Standards

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)