


# Product data sheet

Specifications



## Thorsman - Goliath 250 work lamp - 55 W - CH plug

IMT33002

 **Discontinued on:** Oct 9, 2019

 **Discontinued**

### Main

Range	Thorsman
Product Name	Goliath 250
Product Or Component Type	Work lamp
Light Source	Compact fluorescent tube 55 W

### Complementary

Type Of Installation	Outdoor Indoor
[Ue] Rated Operational Voltage	230...240 V
Plug Pole Configuration	2P + E
Plug Standard	Swiss
Light Source Type	Glare-proof Flicker-proof
Luminous Flux	4000 lm
Bulb Lifespan	8000 h
Colour Rendering Index	R <sub>a</sub> =82
Illuminance	1 m: 1890 lux 3 m: 210 lux
Cable Insulation Material	Neoprene
Housing Material	PC + rubber
Electrical Connection	Feed power cord H07RN-F2x1.0 5 m
Electrical Insulation Class	Class II
Marking	ENEC 14 F
Height	316 mm
Width	316 mm
Depth	91 mm
Net Weight	2.9 kg

### Environment

Environmental Characteristic	Dustproof Waterproof
Ip Degree Of Protection	IP65

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Quality Labels	CE ENEC
Ambient Air Temperature For Operation	-15...50 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	31 cm
Package 1 Width	13 cm
Package 1 Length	30.8 cm
Package 1 Weight	3100 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations