

# Product data sheet

Specifications



## Thorsman - Goliath 250+ work lamp - 55 W - Schuko/F plug - 2 Schuko outlets

IMT33005

! Discontinued

! Discontinued on: Sep 30, 2020

! End-of-service on: Oct 26, 2020

### Main

Range	Thorsman
Product Name	Goliath 250+
Product Or Component Type	Work lamp
Light Source	Compact fluorescent tube 55 W

### Complementary

Type Of Installation	Outdoor Indoor
[Ue] Rated Operational Voltage	230...240 V
Maximum Load Current	16 A
Plug Pole Configuration	2P + E
Plug Standard	Schuko/FR
Number Of Power Socket Outlets	2 x 2P + E, French
Light Source Type	Glare-proof Flicker-proof
Luminous Flux	4000 lm
Bulb Lifespan	8000 h
Colour Rendering Index	R <sub>a</sub> = 82
Illuminance	1 m: 1890 lux 3 m: 210 lux
Cable Insulation Material	Neoprene
Housing Material	PC + rubber
Electrical Connection	Feed power cord H07RN-F3G1.5 5 m
Electrical Insulation Class	Class I
Marking	ENEC 14 F
Height	316 mm
Width	316 mm
Depth	94 mm
Net Weight	3.3 kg

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Characteristic	Waterproof Dustproof
Ip Degree Of Protection	IP54
Quality Labels	ENEC CE
Ambient Air Temperature For Operation	-15...50 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	31 cm
Package 1 Width	13 cm
Package 1 Length	30.8 cm
Package 1 Weight	3.46 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations