



Main

Range	Thorsman
Product name	Goliath 250+
Product or component type	Work lamp
Light source	Compact fluorescent tube 55 W

Complementary

Type of installation	Indoor Outdoor
[Ue] rated operational voltage	230...240 V
Maximum load current	16 A
Plug pole configuration	2P + E
Plug standard	French German
Number of power socket outlets	2 x 2P + E, French/German
Light source type	Flicker-proof Glare-proof
Luminous flux	4000 lm
Bulb lifespan	8000 h
Colour rendering index	Ra=82
Colour temperature	3500 K
Illuminance	1 m : 1890 lux 3 m : 210 lux
Cable insulation material	Neoprene
Housing material	PC + rubber
Electrical connection	5 m H07RN-F3G1.5 mm ² feed power cord
Electrical insulation class	Class I
Marking	F ENEC 14
Height	316 mm
Width	316 mm
Depth	94 mm
Product weight	3.3 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Environmental characteristic	Dustproof Waterproof
IP degree of protection	IP54
Quality labels	ENEC CE
Ambient air temperature for operation	-15...50 °C