



Main

Range	Thorsman
Product name	Goliath 100
Product or component type	Work lamp
Light source	Compact fluorescent tube 21 W

Complementary

Type of installation	Indoor Outdoor
[Ue] rated operational voltage	230...240 V
Plug pole configuration	2P + E
Plug standard	Swiss
Light source type	Glare-proof Flicker-proof
Luminous flux	1300 lm
Bulb lifespan	8000 h
Colour rendering index	Ra=82
Illuminance	1 m : 480 lux 3 m : 50 lux
Cable insulation material	Neoprene
Housing material	PC + rubber
Electrical connection	2.5 m H05RN-F2x1.0 mm ² feed power cord
Electrical insulation class	Class II
Marking	ENEC 14 F
Height	205 mm
Width	209 mm
Depth	70 mm
Product weight	1 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

IP degree of protection	IP54
Quality labels	ENEC CE
Ambient air temperature for operation	-15...50 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1834 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations