

Product data sheet

Specifications



Thorsman - Goliath 38 work lamp - 38 W - CH plug

IMT33015

 **Discontinued on:** Oct 9, 2019

 **Discontinued**

Main

Range	Thorsman
Product Name	Goliath 38
Product Or Component Type	Work lamp
Light Source	Compact fluorescent tube 38 W

Complementary

Type Of Installation	Indoor Outdoor
[Ue] Rated Operational Voltage	230 V
Plug Pole Configuration	2P + E
Plug Standard	Swiss
Luminous Flux	2850 lm
Bulb Lifespan	8000 h
Colour Rendering Index	R _a =82
Illuminance	3 m: 134 lux 1 m: 1210 lux
Cable Insulation Material	Neoprene
Housing Material	PC + rubber
Electrical Connection	Feed power cord H07RN-F2x1.0 5 m
Electrical Insulation Class	Class II
Marking	F ENEC 15
Height	280 mm
Width	280 mm
Depth	90 mm
Net Weight	2.7 kg

Environment

Ip Degree Of Protection	IP54
Quality Labels	CE ENEC
Ambient Air Temperature For Operation	-15...50 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	310 cm
Package 1 Width	104 cm
Package 1 Length	285 cm
Package 1 Weight	3.115 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations