

Product data sheet

Specifications



Thorsman - Goliath 38 work lamp - 38 W - contour plug

IMT33017

⚠ Discontinued on: Mar 21, 2017

⚠ Discontinued

Main

Range	Thorsman
Product Name	Goliath 38
Product Or Component Type	Work lamp
Light Source	Compact fluorescent tube 38 W

Complementary

Type Of Installation	Indoor Outdoor
[Ue] Rated Operational Voltage	230 V
Plug Pole Configuration	2P
Plug Standard	European
Luminous Flux	2850 lm
Bulb Lifespan	8000 h
Colour Rendering Index	R _a =82
Illuminance	3 m: 134 lux 1 m: 1210 lux
Cable Insulation Material	Neoprene
Housing Material	PC + rubber
Electrical Connection	Feed power cord H07RN-F2x1.0 5 m
Electrical Insulation Class	Class II
Marking	ENEC 15 F
Height	280 mm
Width	280 mm
Depth	90 mm
Net Weight	2.7 kg

Environment

Ip Degree Of Protection	IP54
Quality Labels	ENEC CE
Ambient Air Temperature For Operation	-15...50 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	310 cm
Package 1 Width	104 cm
Package 1 Length	285 cm
Package 1 Weight	3115 g