

# Product data sheet

Specifications



## Thorsman - compact fluorescent tube 2D for Goliath 38 - 38 W

IMT33030

 **Discontinued on:** Mar 13, 2022

 **Discontinued**

### Main

Range Of Product	Thorsman
Product Compatibility	Goliath 38
Product Or Component Type	Compact fluorescent tube

### Complementary

Rated Lamp Wattage	38 W
Luminous Flux	2850 lm
Bulb Lifespan	8000 h
Colour Rendering Index	R <sub>a</sub> =82
Colour Temperature	3500 K
Illuminance	1 m: 1210 lux 3 m: 134 lux
Bulb Base	GR10q

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	30.5 cm
Package 1 Length	29.5 cm
Package 1 Weight	302 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations