



### Main

Range of product	Thorsman
Product compatibility	Goliath 38
Product or component type	Compact fluorescent tube

### Complementary

Rated lamp wattage	38 W
Luminous flux	2850 lm
Bulb lifespan	8000 h
Colour rendering index	Ra=82
Colour temperature	3500 K
Illuminance	1 m : 1210 lux 3 m : 134 lux
Bulb base	GR10q

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1834 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications