



Main

Range	Thorsman
Product name	Thorsman Mini 1.3 LED
Product or component type	Handheld work lamp
Light source	COB LED 1.3 W

Complementary

Type of installation	Indoor
[Ue] rated operational voltage	100...240 V
Network type	AC
Network frequency	50/60 Hz
Output voltage	5 V DC 1 A
Battery type	Li-Ion (Lithium-Ion) 1 Ah 3.7 V
Operating time	2.5 h at 110 lm
Plug pole configuration	2P + E
Bulb lifespan	50000 h
Colour rendering index	Ra=70
Colour temperature	6000 K
Illuminance	0.5 m : 80 lux
Provided equipment	USB charger
Height	120 mm
Width	59 mm
Depth	25 mm
Product weight	112 g

Environment

Environmental characteristic	Dustproof
IP degree of protection	IP20
Quality labels	CE
Ambient air temperature for operation	-10...40 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Offer Sustainability

REACH

Reference not containing SVHC above the threshold
Reference not containing SVHC above the threshold

IMT33090 is replaced by:



Products IMT33093

Thorsman Mini 1,5W LED - rechargeable handheld work light (with usb cable)

Qty 1

Reason for Substitution: End of life | Substitution date: 10 August 2017