



### Main

Range	Thorsman
Product name	Thorsman 50 LED
Product or component type	Work lamp
Light source	SMD LED 5630 50 W

### Complementary

Type of installation	Outdoor Indoor
[Ue] rated operational voltage	100...240 V
Network type	AC
Network frequency	50/60 Hz
Plug pole configuration	2P + E
Plug standard	Schuko/FR
Outlet standard	Schuko Nordic
Number of power socket outlets	2 x
Luminous flux	4000 lm
Bulb lifespan	50000 h
Colour rendering index	Ra=80
Beam angle	100 °
Cable insulation material	Neoprene
Material	ABS (acrylonitrile butadiene-styrene) TPE (thermoplastic elastomer)
Electrical connection	3 m H07RN-F3G1.5 mm <sup>2</sup> power cord
Height	300 mm
Width	305 mm
Depth	117 mm
Product weight	2.42 kg

### Environment

Environmental characteristic	Dustproof Splashproof
IP degree of protection	IP54

IK degree of protection	IK07
Quality labels	CE
Ambient air temperature for operation	-25...40 °C

### Offer Sustainability

RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations