


Product data sheet

Specifications



Thorsman 50W LED - worklight DK plug

IMT33110

 **Discontinued on:** Sep 6, 2021

 **Discontinued**

Main

| | |
|---------------------------|-------------------------|
| Range | Thorsman |
| Product Name | Thorsman 50 LED |
| Product Or Component Type | Work lamp |
| Light Source | 120 x SMD LED 5630 50 W |

Complementary

| | |
|--------------------------------|--|
| Type Of Installation | Indoor Outdoor |
| [Ue] Rated Operational Voltage | 100...240 V |
| Network Type | AC |
| Network Frequency | 50/60 Hz |
| Plug Pole Configuration | 2P + E |
| Plug Standard | Denmark |
| Outlet Standard | Denmark |
| Number Of Power Socket Outlets | 2 |
| Luminous Flux | 4000 lm |
| Bulb Lifespan | 50000 h |
| Colour Rendering Index | R _a =80 |
| Beam Angle | 100 ° |
| Cable Insulation Material | Neoprene |
| Material | ABS (acrylonitrile butadiene-styrene) TPE (thermoplastic elastomer) |
| Electrical Connection | Power cord H07RN-F3G1.5 3 m |
| Height | 300 mm |
| Width | 305 mm |
| Depth | 117 mm |
| Net Weight | 2.43 kg |
| Targeted Country | Denmark |

Environment

| | |
|------------------------------|--------------------------|
| Environmental Characteristic | Splashproof Dustproof |
|------------------------------|--------------------------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------------------|-------------|
| Ip Degree Of Protection | IP54 |
| Ik Degree Of Protection | IK07 |
| Quality Labels | CE |
| Ambient Air Temperature For Operation | -25...40 °C |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 30.5 cm |
| Package 1 Width | 11.7 cm |
| Package 1 Length | 30 cm |
| Package 1 Weight | 2.43 kg |

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |