

Product data sheet

Specifications



Cable reel, Thorsman, 40m HO5VVF 2X1.0 IP20, Danish

IMT33160

Main

Range	Thorsman
Range Of Product	PROchantier
Product Name	Thorsman cable reel Advanced
Product Or Component Type	Extension cable reel
Device Application	Power supply
[Ue] Rated Operational Voltage	230 V
[In] Rated Current	13 A
Socket Number	4
Colour Tint	Green/black

Complementary

Outlet Standard	Denmark
Cable Length	40 m
Cable Cross Section	1 mm²
Type Of Cable	H05VV-F2x1
Height	295 mm
Width	377 mm
Depth	220 mm
Net Weight	9.54 kg

Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK08

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	29.0 cm
Package 1 Width	22.5 cm
Package 1 Length	37.0 cm
Package 1 Weight	6.6 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information