



Main

| | |
|---------------------------|--------------------|
| Range of product | Mureva |
| Product name | Mureva BOX |
| Device short name | K60 |
| Product or component type | Junction box |
| Device application | Cable installation |
| Colour tint | White (RAL 9003) |
| Quantity per set | 2 |

Complementary

| | |
|-----------------|-------------------------------------|
| Device mounting | Surface |
| Fixing mode | By screw : body housing |
| Base dimension | 98 x 45 x 65 mm |
| Material | PA (polyamide) 6/PP (polypropylene) |
| Height | 60 mm |
| Width | 60 mm |
| Depth | 30 mm |

Environment

| | |
|---------------------------------------|----------------------------------|
| Ambient air temperature for operation | -25...60 °C |
| IP degree of protection | IP20 |
| Standards | EN 60670-1 |
| Product certifications | NEMKO DEMKO SEMKO FIMKO |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications