



Main

Range of product	Multifix
Product name	Multifix Air
Product or component type	Ceiling box
Device application	Airtight installation
Device presentation	With surface cover
Provided equipment	IPX4 DCL outlet Pre-mounted suspension chimney Hook Surface cover
Quantity per set	Set of 10

Complementary

Function available	Anti-rotation system
Number of gangs	1 gang
Fixing mode	By screws
Material	ABS (acrylonitrile butadiene-styrene) PA (polyamide) 6.6 Steel PC (polycarbonate)/ABS (acrylonitrile butadiene-styrene) PP (polypropylene)/TPE (thermoplastic elastomer)
Mechanical robustness	Fire resistance Airtight
Colour tint	Green NCS S 2070-G80Y
Cable entry	4 knock-out
Drill diameter/depth	67 mm 50 mm
Height	71 mm
Width	71 mm
Depth	49 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ambient air temperature for operation	-5...60 °C
IP degree of protection	IP20
Fire resistance	850 °C
Standards	EN 60670-1

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1839 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------