



## Main

Range of product	Mureva
Product or component type	Rigid conduit
Shape	Plain ends
Function available	GT-function
Mounting location	Indoor Outdoor
Nominal cross section	109 mm <sup>2</sup>
Diameter	External : 16 mm Internal : 11.8 mm
Colour tint	Black (RAL 9005)
Length	3 m

## Complementary

Resistance to compression	1.25 N
Material	PC (polycarbonate)
Quantity per set	75 m
Ambient air temperature for operation	-45...120 °C
Standards	IEC 60754-1 IEC 60754-2 NF F 16-101 NF F 16-102 EN 50267-2-1 EN 50267-2-2 IEC 61386

## Environment

IP degree of protection	IP41 with coupler
IK degree of protection	IK10
Product certifications	NF CSTB

Environmental characteristic	Non-flame propagating
Environmental health and issues	Halogen free LSF (Low Smoke and Flame Retardance)
Flame retardance	M2
Level or class	F1

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1839 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------