



Main

Range of product	Mureva
Product or component type	Rigid conduit
Shape	Plain ends
Function available	GT-function
Mounting location	Indoor Outdoor
Nominal cross section	940 mm ²
Diameter	External : 40 mm Internal : 34.6 mm
Colour tint	Black (RAL 9005)
Length	3 m

Complementary

Resistance to compression	1.25 N
Material	PC (polycarbonate)
Quantity per set	21m
Ambient air temperature for operation	-45...120 °C
Standards	IEC 60754-1 IEC 60754-2 NF F 16-101 NF F 16-102 EN 50267-2-1 EN 50267-2-2 IEC 61386

Environment

IP degree of protection	IP41 with coupler
IK degree of protection	IK10
Product certifications	NF CSTB

Environmental characteristic	Non-flame propagating
Environmental health and issues	Halogen free LSF (Low Smoke and Flame Retardance)
Flame retardance	M2
Level or class	F1

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1839 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------